

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Cofilin antibody produced in rabbit - IgG fraction of antiserum, buffered aqueous solution

Product Number:

C8736

Storage Temperature:

-20 °C

TEST**Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	9.0 - 12.0 mg/ml
WB-Cell Line/Tissue Extract	PC-12 cells
WB Titer	1:10,000-1:20,000
WB-Cell Line/Tissue Extract	A431 Human epithelial carcinoma cells
WB-Western Blot-Titer	1:10,000-1:20,000
WB-Cell Line/Tissue Extract	MDCK
WB-Western Blot Titer	1:10,000-1:20,000
ICC/IF Cells	NIH-3T3 Mouse Fibroblasts
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.2% Triton X-100
ICC/IF-Titer	1:1000-1:2000
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000016940

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.