


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
4-(Benzyloxy)benzyl chloride - 97%

**Product Number:** 114081  
**CAS Number:** 836-42-0  
**MDL:** MFCD00000916  
**Formula:** C<sub>14</sub>H<sub>13</sub>ClO  
**Formula Weight:** 232.71 g/mol  
**Storage Temperature:** 2 - 8 °C



TEST	Specification
Appearance (Color) White to Pink, Yellow or Tan	Conforms to Requirements
Appearance (Form) Powder, Crystals or Crystalline Powder	Conforms to Requirements
Infrared spectrum	Conforms to Structure
Titration by AgNO <sub>3</sub> After Oxygen Combustion	96.5 - 103.5 %

Specification: PRD.0.ZQ5.10000012064

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.