

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Disialoganglioside-GD₂ from bovine brain - ~95%, lyophilized powder, semisynthetic

Product Number:

G0776

CAS Number:

65988-71-8

Storage Temperature:

-20 °C

TEST**Specification**

Appearance (Form)	Conforms
Film (Dried In Situ)	
Solubility (Solvent)	CH ₂ Cl ₂ /MeOH 1/1
Solubility (Conc)	4.90 - 5.10 mg/ml
Solubility (Turbidity)	Clear
Solubility (Color)	Colorless to Faint Yellow
Purity (TLC)	≥ 95.00 %
Vial Content (Size)	100.00 - 100.00
Vial Content (Unit Of Measure)	µg
Vial Content (Actual Content)	≥ 100.00
Vial Content (Overpack)	≤ 25.00 %
Recommended Retest Period	-----
2 Years	

Specification: PRE.1.ZQ5.10000001969

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.