


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Pyrazineethanethiol - $\geq 97\%$, FG

Product Number: W323004
CAS Number: 35250-53-4
MDL: MFCD00053160
Formula: C₆H₈N₂S
Formula Weight: 140.21 g/mol
Storage Temperature: 2 - 8 °C



TEST	Specification
Appearance (Color)	Colorless to Yellow
Appearance (Form)	Liquid
Refractive index at 20 °C	1.565 - 1.569
Infrared spectrum	Conforms to Structure
Purity (GC)	$\geq 97.0\%$
Specific Gravity at 20°C	1.143 - 1.168
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period 5 Years	-----

Specification: PRD.3.ZQ5.1000083918

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

