

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)

Email USA: [techserv@sial.com](mailto:techserv@sial.com)


Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Ionomycin calcium salt from *Streptomyces conglobatus* - powder, ≥98% (HPLC)

Product Number: **I0634**  
CAS Number: 56092-82-1

Formula: C<sub>41</sub>H<sub>70</sub>CaO<sub>9</sub>  
Formula Weight: 747.07 g/mol  
Storage Temperature: 2 - 8 °C



TEST	Specification
------	---------------

Appearance (Form)	Powder
Appearance (Colour)	White to White w/ Yellow Cast
Solubility (Solvent)	Dimethylsulfoxide
Solubility (Conc)	9.80 - 10.20 mg/ml
Solubility (Turbidity)	Clear
Solubility (Color)	Colorless to Faint Yellow
Elemental Anal. (%C anhydrous)	65.35 - 66.35 %
Element Detection (% Ca)	4.0 - 6.0 %
Element Detection (Method)	ICP
NMR (Solvent)	CDCl <sub>3</sub>
Identity by NMR	Consistent
NMR (Residual Solvent 1)	Acetonitrile
NMR (% Solvent 1)	≤ 2.00 %
Purity (HPLC)	≥ 98.00 %
Purity (TLC)	≥ 98.00 %
Recommended Retest Period	-----
3 Years	

Specification: PRE.2.ZQ5.10000001407

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.