

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)

Email USA: [techserv@sial.com](mailto:techserv@sial.com)

Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
1,6-Hexanediol ethoxylate diacrylate - average  $M_n \sim 314$

Product Number: **497134**

MDL: MFCD01863613



Storage Temperature: 2 - 8 °C

TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Infrared spectrum	Conforms to Structure
Ethoxylate/Molecule	2.0 - 3.0
Loss on Drying	≤ 0.50 %
Water (by Karl Fischer)	≤ 0.50 %
Viscosity	10 - 20 cps
Acid Value	≤ 0.50
mg KOH/g	
MEHQ as Inhibitor	200 - 400 ppm

Specification Date : 04/18/2011

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.