


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Oleanolic acid - ≥97%

Product Number: **O5504**
CAS Number: 508-02-1
MDL: MFCD00064914
Formula: C₃₀H₄₈O₃
Formula Weight: 456.70 g/mol
Storage Temperature: 2 - 8 °C



TEST

Specification

Appearance (Color)	White to Light Yellow
Appearance (Form)	Powder
Solubility (Color)	Colorless to Faint Yellow
Solubility (Turbidity)	Clear to Slightly Hazy
10 mg /mL, CHCL ₃	
Infrared spectrum	Conforms to Structure
Water (by Karl Fischer)	≤ 5 %
Purity (TLC)	≥ 97 %
Purity (Titr. by NaOH) anhyd.	≥ 97 %

Specification: PRD.1.ZQ5.10000024072

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.