


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
2-Acetylpyridine - ≥99%, FG

Product Number: W325104
CAS Number: 1122-62-9
MDL: MFCD00006303
Formula: C₇H₇NO
Formula Weight: 121.14 g/mol



TEST

Specification

Appearance (Color)	Colorless to Yellow
May Have a Faint Pink Cast	
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.519 - 1.523
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 99.0 %
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period	-----
5 Years	

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.