

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Monoclonal Anti-Fibronectin antibody produced in mouse - clone IST-4, ascites fluid

Product Number:

F0916

Storage Temperature:

-20 °C

**TEST****Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Very Faint Yellow to Very Dark Yellow to Very Dark Brown
Protein by Biuret	15 - 55
Mouse IgG1 by RID	2.0 - 7.0 mg/ml
WB-Cell Line/Tissue Extract	HS-68 Human Foreskin Fibroblasts Cells
WB Titer	1:250-1:500
ICC/IF Cells	HS-68 Human Foreskin Fibroblasts Cells
ICC/IF Fixation Reagent 1	Methanol
ICC/IF-Fixation Reagent 2	Acetone
ICC/IF-Titer	1:100-1:200
Recommended Retest Period	-----
5 Years	

Specification: PRE.0.ZQ5.10000016423

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.