

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)

Email USA: [techserv@sial.com](mailto:techserv@sial.com)

Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification


Product Name:  
α-Terpinyl acetate - FG

Product Number: **W304799**

CAS Number: 80-26-2

Formula: C<sub>12</sub>H<sub>20</sub>O<sub>2</sub>

Formula Weight: 196.29 g/mol



TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Refractive index at 20 °C	1.464 - 1.467
Infrared Spectrum	Conforms to Structure
GC Purity (sum of isomers)	≥ 95.0 %
Optical Rotation	
c = Neat	
Specification: Report Result	
Specific Gravity	0.950 - 0.970
at 25°C	
Organoleptics	Pass
Arsenic (As)	≤ 3.0 ppm
Cadmium (Cd)	≤ 1.0 ppm
Mercury (Hg)	≤ 1.0 ppm
Lead (Pb)	≤ 10.0 ppm
Expiration Date Period	-----
5 Years	

Specification: PRD.2.ZQ5.1000064457

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.