

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Trypsin Acetylated from bovine pancreas - Type V-S,  $\geq 8,500$  BAEE units/mg protein (biuret)Product Number: **T6763**

MDL: MFCD00082094

Storage Temperature: -20 °C

TEST	Specification
------	---------------

Appearance (Color)

White to Off-White

Appearance (Form)

Powder

% Protein (Biuret)

80 - 100

BAEE units/mg protein

 $\geq 8500$ 

One BAEE unit will produce a delta A253 of 0.001 per minute with BAEE as substrate at pH 7.6 at 25 °C. Reaction volume = 3.2 mL (1cm light path).

Specification: PRD.0.ZQ5.10000050144

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.