

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Mepivacaine hydrochloride - 98.0-102.0%, meets USP testing specifications

Product Number:

M3189

CAS Number:

1722-62-9

MDL:


MFCD00144738

Formula:

C₁₅H₂₂N₂O · HCl

Formula Weight:

282.81 g/mol

**TEST****Specification**

Identity	Pass
Loss on Drying	≤ 1.0 %
Residue on ignition (Ash)	≤ 0.1 %
Purity	Conforms
Chromatographic purity: < or = 0.4%	
Assay	98.0 - 102.0 %
Dry Basis	
Residual Solvents USP 467	Meets Requirements

Specification: PRD.0.ZQ5.10000034964

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.