

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Anti-hnRNP-U antibody, Mouse monoclonal - clone 3G6, purified from hybridoma cell culture

Product Number:

R6278

Storage Temperature:

-20 °C

**TEST****Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	2.0 - 2.5 mg/ml
WB-Cell Line/Tissue Extract	Hela Cells
WB-Working Concentration	0.25 - 0.50 µg/ml
Recommended Retest Period	-----
4 Years	

Specification: PRE.1.ZQ5.10000018485

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.