

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Monoclonal Anti- $\beta$ -Actin antibody produced in mouse – clone AC-74, purified immunoglobulin, buffered aqueous solution

Product Number:

A2228

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	2.0 - 2.5 mg/ml
WB-Cell Line/Tissue Extract	HS-68 Human Fibroblast or Chicken Fibroblast
WB Working Concentration	0.5 - 1.0 $\mu$ g/ml
ICC/IF Cells	HS-68 Human Fibroblast or Chicken Fibroblast
ICC/IF Fixation Reagent 1	Methanol
ICC/IF-Fixation Reagent 2	Acetone
ICC/IF-Working Concentration	10 - 40 $\mu$ g/ml
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000016419

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.