

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Dibenzyl N,N-diisopropylphosphoramidite - technical grade, 90%

Product Number:**416436**

CAS Number:

108549-23-1

MDL:

MFCD00191988

Formula:


C₂₀H₂₈NO₂P

Formula Weight:

345.42 g/mol

Storage Temperature:

2 - 8 °C

**TEST****Specification**

Appearance (Color)

Colorless to Light Yellow

Appearance (Form)

Liquid

Appearance (Clarity)

Clear to Slightly Hazy

Infrared spectrum

Conforms to Structure

Carbon

61.2 - 77.9 %

Nitrogen

3.6 - 4.5 %

Specification: PRD.1.ZQ5.10000033652

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.