


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Benzyl mercaptan - 99%, FG

Product Number: W214701
CAS Number: 100-53-8
MDL: MFCD00004867
Formula: C7H8S
Formula Weight: 124.20 g/mol



TEST	Specification
------	---------------

Appearance (Color)	Colorless to Very Light Yellow and Colorless to Very Light Green
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.574 - 1.578
Infrared Spectrum	Conforms to Structure
Purity (GC)	≥ 98.5 %
Residual Solvent - Toluene	≤ 0.0890 %
Specific Gravity (at 20 deg C)	1.040 - 1.080
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period 5 Years	-----

Specification: PRD.6.ZQ5.10000016802

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.