

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

MegaCell™ Dulbecco's Modified Eagle's Medium - liquid, sterile-filtered, suitable for cell culture

Product Number: **M3942**

Storage Temperature: 2 - 8 °C

TEST	Specification
Appearance (Turbidity)	Clear
Appearance (Form)	Solution
pH	7.0 - 7.6
Osmolality	280 - 310 mOs/kg
Sterility by USP guidelines	Negative
Amino Acid Analysis	Pass
Glucose	4.06 - 4.96 g/l
Endotoxin Level	< 2.0 EU/ml
ICP Major Analysis	Pass
Cell Culture Test	Pass
Chapter 4(D) - pH	Conforms

Product meets European Union requirements for treated technical blood products. Form of treatment pH < /= 5.0 for > /= 2 hours.

Specification: PRD.2.ZQ5.10000038973

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.