

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Fibronectin Type III Connecting Segment Fragment 1-25 - ≥90% (HPLC)

Product Number: F5007
CAS Number: 107978-77-8
MDL: MFCD00214575
Formula: C₁₂₃H₁₉₅N₃₁O₃₉
Formula Weight: 2,732.05 g/mol
Storage Temperature: -20 °C



TEST	Specification
------	---------------

Appearance (Color)	White
Appearance (Form)	Powder
Solubility (Color)	Colorless
Solubility (Turbidity)	Clear
1 mg/mL, H ₂ O	
% Peptide content	≥ 70
by Amino Acid Analysis	
% Purity (HPLC)	≥ 90

Specification: PRD.0.ZQ5.10000070021

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.