

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-CRMP2 antibody produced in rabbit - ~1.0 mg/mL, affinity isolated antibody, buffered aqueous solution

Product Number:

C2993

Storage Temperature:

-20 °C

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	1.0 - 1.5 mg/ml
WB-Cell Line/Tissue Extract	Mouse Brain S1 Frac.
WB Working Concentration	0.1 - 0.2 µg/ml
WB-Cell Line/Tissue Extract	Hela Cells
WB-Working Concentration	0.1 - 0.2 µg/ml
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000019820

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.