

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-GAPDH antibody produced in rabbit - ~1 mg/mL, affinity isolated antibody, buffered aqueous solution

Product Number:

G9545

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	1.0 - 1.5 mg/ml
WB-Cell Line/Tissue Extract	Hela Cells
WB Working Concentration	0.10 - 0.20 µg/ml
IP - Cell /Tissue Lysate	NIH-3T3 Mouse Fibroblasts
IP - Antibody Precipitation	5 - 10 µg
ICC/IF Cells	NRK rat kidney cells
ICC/IF Fixation Reagent 1	Methanol
ICC/IF-Fixation Reagent 2	Acetone
ICC/IF-Working Conc. ug/ml	5 - 10 µg/ml
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000016307

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.