

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)


Email USA: [techserv@sial.com](mailto:techserv@sial.com)

Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Ethyl acetate - natural, ≥99%, FCC, FG

**Product Number:** W241415  
**CAS Number:** 141-78-6  
**MDL:** MFCD00009171  
**Formula:** C<sub>4</sub>H<sub>8</sub>O<sub>2</sub>  
**Formula Weight:** 88.11 g/mol



TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.370 - 1.375
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 99.0 %
Residue on Evaporation	≤ 0.02 %
Specific Gravity	0.894 - 0.898
Acid Value	≤ 5.0 ml
Subs Carbonizable by Hot H <sub>2</sub> SO <sub>4</sub>	Pass
Distillation Range	76.0 - 77.5 °C
Miscellaneous Assay (Methyl Compounds)	Pass
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period 5 Years	-----

Specification: PRD.2.ZQ5.10000014508

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.