

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name: Iodomethane-<sup>13</sup>C,d - contains copper as stabilizer, 99 atom % <sup>13</sup>C, 98 atom % D


Product Number: 652415

CAS Number: 55487-75-7

Formula: <sup>13</sup>CDH<sub>2</sub>I

Formula Weight: 143.94 g/mol

Storage Temperature: 2 - 8 °C



TEST	Specification
Appearance (Clarity)	Clear
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Purity (GC)	≥ 99 %
Proton NMR Spectrum	Conforms
Deuterium NMR Spectrum	Conforms
<sup>13</sup> C NMR Spectrum	Conforms
Proton NMR	≥ 99 %
Water (by Karl Fischer)	≤ 0.5 %
Isotopic Enrichment	≥ 98

Specification: PRD.0.ZQ5.10000069447

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.