

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Anti-Human IgA ( $\alpha$ -chain specific) antibody produced in rabbit - IgG fraction of antiserum, buffered aqueous solutionProduct Number: **19889**

Storage Temperature: -20 °C

**TEST****Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	8.0 - 15.0 mg/ml
Antibody Concentration(Method)	Quantitative Precipitin Assay
Antibody Concentration-Antigen	Human Serum
Antibody Concentration	2.5 - 5.0 mg/ml
Antibody Concentration-Antigen	Human Whey
Antibody Concentration	4 - 6 mg/ml
Recommended Retest Period	-----
4 Years	

Specification: PRE.1.ZQ5.10000019197

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.