

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Anti-Mouse IgG (Fab specific) F(ab')<sub>2</sub> fragment-FITC antibody produced in goat - flow cytometry grade, affinity isolated antibody, buffered aqueous solution

Product Number:

**F2653**

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Yellow
F(ab) <sub>2</sub> Concentration(OD 280nm)	1.5 - 3.5 mg/ml
F/P Molar Ratio	1.5 - 3.5
IHC - Tissue	Human Appendix or Human Tonsil
IHC - Fixation	FFPE-Formalin Fixed Paraffin Embedded
IHC - Titer	1:160-1:320
FACS -Cells	Human Blood
FACS-Titer	1:100-1:200
Recommended Retest Period	-----
3 Years	

Specification: PRE.0.ZQ5.10000016638

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.