

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Anti-Human IgA ( $\alpha$ -chain specific)–Peroxidase antibody produced in goat – affinity isolated antibody

Product Number:

A0295

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Brown
IgG Concentration (OD 280nm)	4.0 - 11.0 mg/ml
Molar Ratio P/E	0.6 - 1.5
ELISA - Titer	1:50,000-1:60,000
Dot Blot-Titer	1:80,000-1:160,000
IHC - Tissue	Human Tonsil
IHC - Fixation	FFPE-Formalin Fixed Paraffin Embedded
IHC - Titer	1:100-1:200
Recommended Retest Period	-----
2 Years	

Specification: PRE.0.ZQ5.10000015311

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.