


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Phenethyl acetate - ≥98%, FCC, FG

Product Number: **W285706**
CAS Number: 103-45-7
MDL: MFCD00008720
Formula: C₁₀H₁₂O₂
Formula Weight: 164.20 g/mol



TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.497 - 1.501
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 98.00 %
Specific Gravity	1.030 - 1.034
Acid Value	≤ 1.0 ml
Solubility (Turbidity)	Clear to Very Slightly Hazy
Solubility (Color)	Colorless
1ml/2ml,70% Ethanol(remains clear on dilution to 10ml)	
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period	-----
5 Years	

Specification: PRD.1.ZQ5.10000010329

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.