


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Cyclohexyl acetate - ≥98%, FG

Product Number: W234907
CAS Number: 622-45-7
MDL: MFCD00003850
Formula: C₈H₁₄O₂
Formula Weight: 142.20 g/mol



| TEST | Specification |
|----------------------------|-----------------------|
| Appearance (Color) | Colorless |
| Appearance (Form) | Liquid |
| Refractive index at 20 ° C | 1.437 - 1.441 |
| Infrared spectrum | Conforms to Structure |
| Purity (GC) | ≥ 98.0 % |
| Arsenic (As) | ≤ 3 ppm |
| Cadmium (Cd) | ≤ 1 ppm |
| Mercury (Hg) | ≤ 1 ppm |
| Lead (Pb) | ≤ 10 ppm |
| Organoleptics | Pass |
| Expiration Date Period | ----- |
| 5 Years | |

Specification: PRD.2.ZQ5.1000008635

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

