

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anisomycin, Ready Made Solution from Streptomyces griseolus - 10 mg/mL in DMSO, 0.2 µm filtered

Product Number:

A5862

Formula:

C₁₄H₁₉NO₄

Formula Weight:

265.30 g/mol

Storage Temperature:

-20 °C

TEST	Specification
------	---------------

Appearance (Form)

Liquid

Appearance (Turbidity)

Clear

Appearance (Colour)

Colorless to Light Yellow

Concentration (mg/ml)

10.00 - 11.00 mg/ml

Purity (HPLC)

≥ 98.0 %

Recommended Retest Period

5 Years

Specification: PRE.1.ZQ5.10000002716

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.