


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Benzenesulfonyl isocyanate - 95%

Product Number: 232297
CAS Number: 2845-62-7
MDL: MFCD00007546
Formula: C₇H₅NO₃S
Formula Weight: 183.18 g/mol
Storage Temperature: 2 - 8 °C



TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Infrared spectrum	Conforms to Structure
Titration by AgNO ₃	≤ 1.2 %
After Oxygen Combustion, % Cl	
Purity (GC)	≥ 94.5 %

Specification: PRD.2.ZQ5.10000005374

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.