


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Iodoacetamide - BioUltra

Product Number: **I1149**
CAS Number: 144-48-9
MDL: MFCD00008028
Formula: C₂H₄INO
Formula Weight: 184.96 g/mol
Storage Temperature: 2 - 8 °C



TEST	Specification
Appearance (Color)	White to Off-White
Appearance (Form)	Powder
Solubility (Color)	Colorless
Solubility (Turbidity)	Clear
0.5 M, H ₂ O	
Identity by NMR	Conforms to Structure
Insoluble matter	≤ 0.1 %
Chloride Content	≤ 0.05 %
Sulfate	≤ 0.05 %
Aluminum (AL)	≤ 0.0005 %
Phosphorus (P)	≤ 0.0005 %
Lead (Pb)	≤ 0.001 %
Ammonia (NH ₄)	≤ 0.05 %
Calcium (Ca)	≤ 0.0005 %
Magnesium (Mg)	≤ 0.0005 %
Sodium (Na)	≤ 0.05 %
Copper (Cu)	≤ 0.0005 %
Iron (Fe)	≤ 0.0005 %
Zinc (Zn)	≤ 0.0005 %
Potassium (K)	≤ 0.005 %
NMR (% Purity)	≥ 99 %
Recommended Retest Period	-----
3 years	

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Iodoacetamide - BioUltra

Product Number: I1149
CAS Number: 144-48-9
MDL: MFCD00008028
Formula: C₂H₄INO
Formula Weight: 184.96 g/mol
Storage Temperature: 2 - 8 °C



TEST

Specification

Specification: PRD.5.ZQ5.10000005715

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.