


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Resorcinol – BioXtra, ≥99%

Product Number: R5645  
CAS Number: 108-46-3  
MDL: MFCD00002269  
Formula: C<sub>6</sub>H<sub>6</sub>O<sub>2</sub>  
Formula Weight: 110.11 g/mol



TEST	Specification
Appearance (Color)	White to Off-White
Appearance (Form)	Powder
Solubility (Turbidity)	Clear
1M, Methanol at 20 Degrees Celsius	
Solubility (Color)	Colorless to Faint Yellow
Residue on Ignition	≤ 0.1 %
Insoluble matter	≤ 0.1 %
Aluminum (Al)	≤ 0.0005 %
Calcium (Ca)	≤ 0.0005 %
Copper (Cu)	≤ 0.0005 %
Iron (Fe)	≤ 0.0005 %
Potassium (K)	≤ 0.005 %
Magnesium (Mg)	≤ 0.0005 %
Sodium (Na)	≤ 0.005 %
Phosphorus (P)	≤ 0.005 %
Lead (Pb)	≤ 0.001 %
Zinc (Zn)	≤ 0.0005 %
Purity (GC)	≥ 99.0 %
Ammonia (NH <sub>3</sub> )	≤ 0.05 %
Chloride (Cl)	≤ 0.05 %
Sulfate (SO <sub>4</sub> )	≤ 0.05 %
Recommended Retest Period	-----
6 Years	

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Resorcinol – BioXtra, ≥99%

Product Number: **R5645**  
CAS Number: 108-46-3  
MDL: MFCD00002269  
Formula: C<sub>6</sub>H<sub>6</sub>O<sub>2</sub>  
Formula Weight: 110.11 g/mol



### TEST

### Specification

Specification: PRD.3.ZQ5.10000008988

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.