


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Methyl 4-(hydroxymethyl)benzoate - 98%

Product Number: **266477**
CAS Number: 6908-41-4
MDL: MFCD00009984
Formula: C₉H₁₀O₃
Formula Weight: 166.17 g/mol



TEST	Specification
Appearance (Color)	White to Off White
Appearance (Form)	Powder or Chunks
Initial Melting Point	≥ 47 °C
Final Melting Point	≤ 51 °C
Infrared spectrum	Conforms to Structure
Carbon	63.43 - 66.68 %
Purity (TLC)	≥ 98 %
Solubility (Turbidity)	Clear
Solubility Concentration: 25 mg/mL in Chloroform	
Solubility (Color)	Colorless to Light Yellow
Solubility Concentration: 25 mg/mL in Chloroform	

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.