

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Trizma® base – anhydrous, free-flowing, Redi-Dri™, ≥99.9%

Product Number: RDD008
CAS Number: 77-86-1
Formula: C₄H₁₁NO₃
Formula Weight: 121.14 g/mol



TEST	Specification
ICP-MS (Total: Ag, As, Bi, Cd, Cu, Hg, Mo, Pb, Sb, Sn)	≤ 2 ppm
Appearance (Color)	White
Appearance (Form)	Crystalline Powder
Solubility (Color)	Colorless
Solubility (Turbidity)	Clear
200 g plus 300 ml of H ₂ O	
Infrared spectrum	Conforms to Structure
Water (by Karl Fischer)	≤ 0.2 %
UV Absorbance 290nm	≤ 0.05
40% (w/w)	
Iron (Fe)	≤ 1 ppm
ICP atomic emission	
Initial Melting Point	≥ 168 °C
Final Melting Point	≤ 172 °C
Titration with H ₂ SO ₄	≥ 99.9 %
(Anhydrous)	

Specification: PRD.4.ZQ5.10000045165

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.