

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Histone Deacetylase 4 (HDAC4) (ML-19) antibody produced in rabbit - affinity isolated antibody, buffered aqueous solution

Product Number:

H9411

Storage Temperature:

-20 °C

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	1.0 - 1.5 mg/ml
WB-Cell Line/Tissue Extract	Rat Brain
Western Blot-Titer	1:500-1:1000
WB-Cell Line/Tissue Extract	NIH-3T3 Mouse Fibroblasts
WB-Western Blot-Titer	1:1000-1:2000
IP - Cell /Tissue Lysate	Hela Cells Nuclear Fr.
IP - Antibody Precipitation	10 - 20 µg/tst
ICC/IF Cells	Hela Cells
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.5% Triton X-100
ICC/IF-Titer	1:250-1:500
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000017916

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.