

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.com


Email USA: techserv@sial.com

Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
PIPES – BioPerformance Certified, suitable for cell culture

Product Number: P1851
CAS Number: 5625-37-6
MDL: MFCD00006159
Formula: C₈H₁₈N₂O₆S₂
Formula Weight: 302.37 g/mol



TEST	Specification
ICP-MS (Total: Ag, As, Bi, Cd, Cu, Hg, Mo, Pb, Sb, Sn)	≤ 5 ppm
Appearance (Color)	White
Appearance (Form)	Crystalline Powder
Solubility (Color)	Colorless
Solubility (Turbidity) 20 g plus 80 mL, 1 N NaOH	Clear
Infrared spectrum	Conforms to Structure
UV Absorbance 290nm 20% W/W in 1 N NaOH	≤ 0.1
Titration with H ₂ SO ₄	≥ 99 %
DNAse, Exonuclease Detection	None Detected
NICKase, Endonuclease Detection	None Detected
RNAse Detection	None Detected
Protease Detection	None Detected
Endotoxin Level	≤ 0.1 EU/mg
Total Aerobic Microbial Count	≤ 100 CFU/g
Cell Culture Test	Pass
Recommended Retest Period 2 years	-----

Specification: PRD.2.ZQ5.10000038535

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.