


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
4-Aminophenyl α -D-mannopyranoside

Product Number: **A1394**
CAS Number: 34213-86-0



Formula: C₁₂H₁₇NO₆
Formula Weight: 271.3 AMU

TEST	Specification
------	---------------

Appearance (Form)	Powder
Appearance (Colour)	White to White w/ Yellow Cast
Solubility (Solvent)	Water
Solubility (Conc)	49.00 - 51.00 mg/ml
Solubility (Heating)	Yes
Solubility (Turbidity)	Clear
Solubility (Color)	Colorless to Faint Yellow
Specific Rotation (Solvent)	Methanol
Specific Rotation (Conc)	9.00 - 11.00 mg/ml
Specific Rotation (Alpha D)	123.00 - 135.00 deg
Purity (TLC)	≥ 98.00 %
NMR (Solvent)	D ₂ O
Identity by NMR	Consistent
Water (by Karl Fischer)	
Elemental Anal. (%C anhydrous)	52.63 - 53.63 %
Elemental Anal. (%N anhydrous)	4.66 - 5.66 %
Recommended Retest Period	-----
3 Years	

Specification: PRE.0.ZQ5.1000006488

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.