

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-GM130 (C-terminal) antibody produced in rabbit – affinity isolated antibody, buffered aqueous solution

Product Number:

G7295

Storage Temperature:

-20 °C

TEST**Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	1.0 - 1.4 mg/ml
WB-Cell Line/Tissue Extract	NRK rat kidney cells
WB Working Concentration	0.1 - 0.2 µg/ml
IP - Cell /Tissue Lysate	Hela Cells
IP - Antibody Precipitation	2 - 4 µg/tst
IP Cell /Tissue Lysate	NIH-3T3 Mouse Fibroblasts
IP - Antibody Precipitation	2 - 2 µg
ICC/IF Cells	NRK rat kidney cells
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.5% Triton X-100
ICC/IF-Working Concentration	0.2 - 0.4 µg/ml
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000016738

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.