

3050 Spruce Street, Saint Louis, MO 63103, USA  
Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)  
Email USA: [techserv@sial.com](mailto:techserv@sial.com)  
Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

Product Specification

Product Name:  
Anti-Actin, N-terminal antibody produced in rabbit – ~0.5 mg/mL, affinity isolated antibody, buffered aqueous solution  
Product Number: A2103

TEST	Specification
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Clear
WB-Cell Line/Tissue Extract	Rat Skeletal Muscle
WB-Working Concentration	2.0 - 4.0 µg/ml
WB-Cell Line/Tissue Extract	Hela Cells
WB Working Concentration	0.5 - 1.0 µg/ml
ICC/IF Cells	Chicken Fibroblast
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.5% Triton X-100
ICC/IF-Working Conc. ug/ml	1.0 - 2.0 µg/ml
IHC - Tissue	Mouse Heart
IHC - Working Concentration	2 - 4 µg/ml
IHC -Tissue	Frog Muscle
IHC-Working Concentration	2 - 4 µg/ml
IHC -Tissue	Human Appendix
IHC - Working Concentration	2 - 4 µg/ml
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000015971

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.