

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.com

Email USA: techserv@sial.com

Outside USA: eurtechserv@sial.com

Product Specification

Product Name:

Cyclosporin A – from Tolypocladium inflatum, BioReagent, for molecular biology, ≥95%

Product Number:

C1832

CAS Number:


59865-13-3

Formula:

C₆₂H₁₁₁N₁₁O₁₂

Formula Weight:

1,202 AMU



TEST

Specification

Appearance (Form)	Powder
Appearance (Colour)	White to White w/ Yellow Cast
Solubility (Solvent)	Dichloromethane
Solubility (Conc)	9.80 - 10.20 mg/ml
Solubility (Turbidity)	Clear
Solubility (Color)	Colorless to Faint Yellow
Water (by Karl Fischer)	≤ 5.00 %
Elemental Anal. (%C anhydrous)	61.42 - 62.42 %
Elemental Anal. (%N anhydrous)	12.31 - 13.31 %
Purity (HPLC)	≥ 95.00 %
NMR (Solvent)	CDCl ₃
Identity by NMR	Consistent
NMR (Residual Solvent 1)	Dichloromethane
NMR (% Solvent 1)	≤ 3.00 %
NMR (Residual Solvent 2)	Hexane
NMR (% Solvent 2)	≤ 0.50 %
Suitability (Result)	Pass
Suitability (Test)	IL-2 Inhib./Jurkat
Recommended Retest Period	-----
2 Years	

Specification: PRE.0.ZQ5.10000002261

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.