


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
CHES - BioXtra, ≥99.0% (titration)

Product Number: **C8210**  
CAS Number: 103-47-9  
MDL: MFCD00003835  
Formula: C<sub>8</sub>H<sub>17</sub>NO<sub>3</sub>S  
Formula Weight: 207.29 g/mol



TEST	Specification
------	---------------

Appearance (Color)	White
Appearance (Form)	Powder
Solubility (Color)	Colorless
Solubility (Turbidity) (0.5 M, H <sub>2</sub> O)	Clear
Water (by Karl Fischer)	≤ 1 %
pH (c = 0.5 M)	3.0 - 5.0
Ammonia (NH <sub>3</sub> )	≤ 0.05 %
Residue on ignition (Ash)	≤ 0.1 %
Chloride (Cl)	< = 0.05%
Sulfate (SO <sub>4</sub> )	≤ 0.05 %
Insoluble matter	≤ 0.1 %
Aluminum (AL)	≤ 0.0005 %
Phosphorus (P)	≤ 0.0005 %
Lead (Pb)	≤ 0.001 %
Iron (Fe)	≤ 0.0005 %
Copper (Cu)	≤ 0.0005 %
Zinc (Zn)	≤ 0.0005 %
Calcium (Ca)	≤ 0.001 %
Magnesium (Mg)	≤ 0.0005 %
Sodium (Na)	≤ 0.01 %
Potassium (K)	≤ 0.005 %

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
CHES - BioXtra, ≥99.0% (titration)

Product Number: **C8210**  
CAS Number: 103-47-9  
MDL: MFCD00003835  
Formula: C<sub>8</sub>H<sub>17</sub>NO<sub>3</sub>S  
Formula Weight: 207.29 g/mol



TEST	Specification
A260 UV Absorption (0.5 M Solution)	≤ 0.08
A280 UV Absorption (0.5 M Solution)	≤ 0.05
Titration with NaOH Anhydrous	≥ 99.0 %
Recommended Retest Period 3 years	-----

Specification: PRD.1.ZQ5.10000075381

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.