

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Human IgA (α -chain specific) antibody produced in goat - affinity isolated antibody, lyophilized powderProduct Number: **I0884**

MDL: MFCD00162412

Storage Temperature: 2 - 8 °C

TEST	Specification
Appearance (Color)	White to Off-White
Appearance (Form)	Solid
Solubility (Turbidity)	Clear to Slightly Hazy
after reconstitution to 1 mg/ml with 0.135 M NaCl	
Solubility (Color)	Colorless
after reconstitution to 1 mg/ml with 0.135 M NaCl	
Solubility (Form)	Solution
after reconstitution to 1 mg/ml with 0.135 M NaCl	
Protein Concentration by E280	1.00 - 1.50 mg/ml
Specificity by IEP	Conforms
Single arc of precipitation in the gamma-region when 100 μ g is reacted versus 5 μ l of normal human serum containing bromphenol blue and 5 μ g normal human IgA.	
Purity by IEP	Conforms
Single arc of precipitation in the gamma-region when 5 μ g is reacted versus 100 μ l of anti-goat whole serum and 100 μ l of anti-goat IgG.	
Ouchterlony Double Diffusion	Conforms
Cross-reactivity:	
Line of identity when 25 μ g is reacted versus 10 μ g of human IgA kappa and human IgA lambda.	
No reaction when 25 μ g is reacted versus 10 μ g of normal human IgM, normal human IgG, Bence Jones kappa, and Bence Jones lambda.	
Titer by SRID	0.5 - 5.0 mg/ml
1 mg will react with 0.5-5.0 mg of normal Human IgA	

Specification: PRD.1.ZQ5.10000006747

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.