

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Phenol:Chloroform:Isoamyl Alcohol 25:24:1 Saturated with 10 mM Tris, pH 8.0, 1 mM EDTA. – Supplied with Equilibration buffer, for molecular biology

Product Number:

P2069

Storage Temperature:

2 - 8 °C

TEST	Specification
Appearance (Turbidity)	Colorless
Appearance (Form) 2 layer	Liquid
Purity	≥ 99.0 %
UV Absorbance 330nm	≤ 0.2
UV Absorbance 405nm	≤ 0.1
UV Absorbance 510nm	≤ 0.1
pH 25°C	6.5 - 6.9
DNAse, RNAse, and Protease	None Detected

Specification: PRD.0.ZQ5.10000063417

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.