

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

[3aS-(3a α ,4 α ,5 β ,7a α)]-5-Azido-7-bromo-3a,4,5,7a-tetrahydro-2,2-dimethyl-1,3-benzodioxol-4-ol - 99%

Product Number:

493406

CAS Number:

171916-75-9

MDL:

MFCD01863546

Formula:


C₉H₁₂BrN₃O₃

Formula Weight:

290.11 g/mol

Storage Temperature:

-20 °C



TEST

Specification

Appearance (Color)

White

Appearance (Form)

Powder or Crystals

Infrared spectrum

Conforms to Structure

Optical Rotation

20.0 - 28.0 deg

c = 1%, CHCl₃Titration by AgNO₃

98.5 - 101.5 %

After Oxygen Combustion

Specification: PRD.0.ZQ5.10000055489

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.