

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Anti-Histone Deacetylase 7 (HDAC7) (KG-17) antibody produced in rabbit - affinity isolated antibody, buffered aqueous solution

Product Number:

H2662

Storage Temperature:

-20 °C

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	1.0 - 1.5 mg/ml
WB-Cell Line/Tissue Extract	NIH-3T3 Mouse Fibroblasts
WB Titer	1:1000-1:2000
IP - Cell /Tissue Lysate	293-T Cells Exp Human HDAC7
IP - Antibody Precipitation	1.0 - 1.5 µg/tst
ICC/IF Cells	NRK rat kidney cells
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.5% Triton X-100
ICC/IF-Titer	1:50-1:100
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000017913

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.