

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

NADase from porcine brain - ≥ 0.007 unit/mg solid

Product Number:

N9879

CAS Number:

9032-65-9

MDL:

MFCD00131705

Storage Temperature:

-20 °C

TEST	Specification
------	---------------

Appearance (Color)

Off White to Light Beige to Light Brown

Appearance (Form)

Powder

Solubility (Color)

White to Yellow

Solubility (Form)

Suspension

at 6.2 mg/mL in 0.1M potassium phosphate, pH 7.3

units/mg solid

 ≥ 0.007

One unit will hydrolyze 1.0 micromole of beta-NAD to nicotinamide and ADP-Ribose per minute at pH 7.3 at 37 deg C

Method: SS-NAD07

Suggested control: N9879(DF)

Run two samples

Specification: PRD.1.ZQ5.10000066043

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.